

广州优尼卡塑料容器有限公司 GUANGZHOU UNOCAL PLASTIC CONTAINER CO.,LTD



地址: 广州市从化区太平镇福从路22号

# GNOCAL





### (FUOCAL

广州优尼卡塑料容器有限公司是一家集产品设计、模具制造、注塑成型、吹塑成型、丝印烫金、电镀喷涂、自动组装为一体的化妆品塑料包装生产企业。

公司地处美丽富饶、工业发达、开放进取的中国广州,公司自建工业园区,自建工业净化车间厂房面积2.8万平方米,是国内同行业中技术领先,产品种类齐全的生产企业之一。公司十分重视产品创新,以不断开发新产品及开拓应用域,来满足世界各地的消费者及客户的需要。公司产品远销欧、美、东南亚等国家和地区,与国际国内化妆品企业形成配套服务产业链。

公司拥有多台国际水平的日精全电动精密注塑机,长飞亚全电动精密注塑机,ASB高精度注吹一体机,夏米尔CNC加工中心,夏米尔镜面火花机,法朗客数控车床,全自动印刷机,自动烫金机,自动组装机等设备,并提供从产品设计、制模、试样到生产,丝印、烫金、涂装等一站式采购。同时公司拥有一支力量维厚的技术、生产队伍及一套行之有效的管理制度,尤其品质体系里精益求精的QC团队,不仅一丝不苟,还通过光影360全方位检测机,三次元检测机等先进设备,对产品关键部件100%全自动检测,确保产品品质,是提升企业形象的有力保证。

公司现已形成年生产近6000万套各类塑料滴管瓶、厚身PET吹瓶、普通PET瓶、真空瓶、双腔滴管瓶、双腔分配器、广口瓶等不同瓶型的生产规模,年销售额亿元,本公司以诚信、务实为宗旨,以顾客满意为导向,以产品创新为动力,博取众长,开创新高,愿我们的协作使您锦上添花,从而达到"共创共赢"的双赢局面。


Guangzhou Unocal Plastic Container Co., Ltd. is a cosmetic plastic packaging production company that integrates product design, mold manufacturing, injection molding, blow molding, screen printing, hot stamping, electroplating and spraying, and automatic assembly.

Located in the beautiful, rich, industrially developed, and open-minded city of Guangzhou, China, the company has its own industrial park and a factory area of 28,000 square meters. It is one of the leading technology companies in the industry with a complete range of products. The company places great emphasis on product innovation and continuously develops new products and explores new applications to meet the needs of consumers and customers worldwide. The company's products are exported to Europe, America, Southeast Asia, and other countries and regions and have formed a supporting service industry chain with international and domestic cosmetic companies.

The company has multiple international-level precision injection molding machines, including JSW all-electric injection molding machines, Chenhsong all-electric injection molding machines, ASB high-precision injection blow molding machines, Sharmill CNC machining centers, Sharmill mirror spark machines, Fanuc CNC lathes, fully automatic printing machines, hot stamping machines, and automatic assembly machines. The company provides one-stop procurement services from product design, mold making, sample production to production, screen printing, hot stamping, and coating. At the same time, the company has a strong technical and production team and an effective management system, especially the QC team that pursues excellence in the quality system. They strictly inspect products' critical components through advanced equipment such as light and shadow 360-degree detection machines and three-dimensional inspection machines to ensure product quality, which is a powerful guarantee for improving the company's image.

The company has now formed a production scale of nearly 60 million sets of various plastic dropper bottles, thick PET blow-molded bottles, ordinary PET bottles, vacuum bottles, double-cavity dropper bottles, double-cavity distributors, wide-mouth bottles, and other different bottle types. The annual sales volume is 100 millions of RMB The company is guided by integrity and pragmatism, customer satisfaction-oriented, product innovation-driven, and open to learning from others to create new heights. We hope that our cooperation will add luster to your business and achieve a win-win situation of "co-creation and sharing."







03

双腔混合系列 Duo-Mix Series



### 滴管 Dropper

- -20牙厚壁滴管
- 20Neck Heavy-wall Dropper -26牙厚壁滴管
- 26Neck Heavy-wall Dropper -滴管精华瓶
- Ampoule Dropper



#### 广口瓶 Jar

- -广口瓶-A&E JAR A&E
- -厚壁PET广口瓶 HEAVY-WALL PET JAR



### PRODUCT

CATALOG

产品目录



-DCD

### <u>24</u>


#### PET吹瓶 PET Bottle

- -PET化妆水瓶 PET Toner Bottle
- -PET吹瓶
- PET Lotion Bottle



### **DUO-MIX AMPOULE DROPPER**

CAP: PP Ring: ABS Outer: PETG Inner: PP





### **DUO-MIX DROPPER**

### 双腔混合伸缩滴管

CAP: PETG Collar: PETG

Outer: Heavy-wall PET Inner: PP


Step i	216	pZ S	step3
<b>₹</b>	E ml	(Z) mm	□‡ mm
	3+20	Ø35	89
	3+30	Ø35	104
	3+30	Ø42	104



### **DUO-MIXED BOTTLE**

双腔混合瓶

CAP: PETG CHAMBER: PETG BOTTLE: AS/PETG/HEAVY-WALL PET



0.3



### **DUO-MIXED BOTTLE**

### 双腔混合瓶

CAP: PETG CHAMBER: PETG BOTTLE: PET/HEAVY-WALL PET



.05



### DROPPER 20NECK HEAVY-WALL DROPPER

滴管-20牙厚壁滴管

BOTTLE: HEAVY-WALL PET

			□ Imm
a.	20	Ø33	79.0
	30	Ø38	86.0
U	50	Ø38	105.0
Д	30	Ø36	96.0
	50	Ø39	105.5
Д	30	Ø37	96.0
	50	Ø40	103.4
47	30	Ø38	88.6
	50	Ø38	108.6
Д	30	Ø46	87.5
	50	Ø46	105.0



### DROPPER 20NECK HEAVY-WALL DROPPER

滴管-20牙厚壁滴管

BOTTLE: HEAVY-WALL PET

₹/>	E m	⊘ mm	₩Ţmm	# Imm
Д.	20	Ø33	83	87.2
	30	Ø38	90	94.2
	50	Ø38	109	113.2
Д	30	Ø36	100.1	104.3
	50	Ø39	109.5	113.7
Д	30	Ø37	100.1	104.3
	50	Ø40	107.5	111.7
<del>-</del>	30	Ø38	92.8	97.1
	50	Ø38	112.8	117
Д	30	Ø46	91.5	95.8
	50	Ø46	109	113.2

.09



### DROPPER 26NECK HEAVY-WALL DROPPER

滴管-26牙厚壁滴管

BOTTLE: HEAVY-WALL PET

4	E mi	⊘ mm	A:mm	A‡mm
	20	Ø33	77.3	92.3
	30		95.3	110.3
	50	Ø37	100.0	115



## DROPPER AMPOULE DROPPER

滴管-滴管精华瓶

CAP: PP OTTLE: PETG

₹ <i>⁄</i> >	E ml	⊘ mm	□‡ mm
	10	Ø26	70.3
Н	15	020	88.6

11 12\_



### JAR A&E



CAP: PETG/ABS OUTER: PS/AS INNER: PP

4>	E ml	⊘ mm	□] mm
	15	Ø53.7	29.8
	30		40.4
	50		56.2
	15/20	255	36.6
	30	Ø55	46.6
	50	Ø65	56.0



### **HEAVY-WALL PET JAR**



CAP: PETG/AL LID: LLDPE JAR: HEAVY-WALL PET


<b>₽</b>	E mi	⊘ mm	□ţ mm
	30	Ø54	36.8
	50	Ø64	43.6
	30	Ø54	35
	50	Ø64	41
	30	Ø54	35.3
	50	Ø64	42
	30	Ø54	33
	50	Ø64	39



### AIRLESS BOTTLE SVD



CAP: PETG COLLAR: PP/ABS BOTTLE: PETG





### **AIRLESS BOTTLE SVD33**

真空瓶-SVD33

CAP: PETG COLLAR: PP/ABS BOTTLE: PETG


<b>€</b> >			□‡ mm
	20		98.5
	30		116.4
	40	Ø33	134.4
	50		152.2
5	20		98.5
	30		116.4
	40		134.4
Ш	50		152.2



### AIRLESS BOTTLE FVD



CAP: PETG COLLAR: PETG BOTTLE: PETG





### AIRLESS BOTTLE TVD



CAP: PETG COLLAR: PP/ABS BOTTLE: PETG


			□‡ mm
昌	30	Ø41	99.3
	50		115.7
	100		162.7



### DOUBLE-WALL AIRLESS BOTTLE PY & PH

### 双层真空瓶-PY & PH

CAP: PETG COLLAR: PP/PETG OUTER: AS INNER: PP/PETG






### DOUBLE-WALL AIRLESS BOTTLE PA & PD

双层真空瓶-PA & PD

CAP: PETG COLLAR: ABS OUTER: PS INNER: PP

<b>₩</b>		⊘ mm	□[ mm
A	20		105.1
	30	Ø37	127.5
昌	20	637	104.5
	30		126.7
A	20	Ø43	115.8
	30	Ø45	140.7
昌	20	Ø43	116.6
U	30	Ø45	141.6



#### **DUAL TUBE AIRLESS BOTTLE-DCD**

### 双管真空瓶-DCD

CAP: PETG COLLAR: PP OUTER: AS/ABS INNER: PP

4>	₽ ml	⊘ mm	□ţ mm
	10×2	Ø48	113.3
	15×2	040	113.3
Ш	30×2	Ø59	141.3



### PET TONER BOTTLE

PET化妆水瓶

CAP: PETG BOTTLE: PET

	50	Ø33	92.8
	80	W33	131.7
$\mathbf{H}$	80		97.7
	100	Ø41	114.0
Ш	120	641	127.4
	150		153.3
	100	Ø37	147.6
	80	Ø41	107.3
	100	Ø41	123.7
	120	Ø41	137.0
	150	Ø41	162.9



### PET LOTION BOTTLE

PET吹瓶

CAP: PETG COLLAR: PP/ABS BOTTLE: PET

<b>₹</b> />	E mi	⊘ mm	□[ mm
	50	Ø33	118.0
	80		156.9
	50	Ø41	98.3
	80		120.5
	100		137.5
	120		151.3
	150		177.3

\_ 23

